

VistaMount™ is a white 100µ (4 mil) Dry Mounting Tissue with a buffered paper carrier coated with a pH neutral heat activated adhesive.

- IDEAL WHERE THERE IS A NEED TO REDUCE SHOW THROUGH FROM THE BACKING MATERIAL I.E SHOW THROUGH IS SIGNIFICANTLY REDUCED WHEN MOUNTING TO BLACK GATORFOAM®

PRODUCT STRUCTURE

Adhesive	Solvent Acrylic (Heat Activated) Neutral pH
Film	White Buffered Paper
Adhesive	Solvent Acrylic (Heat Activated) Neutral pH

PRODUCT CHARACTERISTIC

Film Thickness	4 mil (100µ)	6 mil (150µ)
Adhesive Layer	1 mil (25µ) on each side	
Film/Adhesive Ratio	1:4:1	
UV Protection Factor	Not Applicable	
Outdoor Durability	Not Applicable	
Service Temperature Range	-4°F to 203°F (-20°C to 95°C)	
Shelf Life	2 Years	
Storage Conditions	59°F to 72°F (15°C to 22°C); 50 - 55% Relative Humidity	

PROCESS SETTINGS

Equipment Type & Temperature	Speed
Roller Laminator Not Recommended	
Press 165°F to 195°F (77°C to 91°C)	Dwell Time: 60 - 90 seconds

DRYTAC®
ADHESIVE SCIENCE

For more information,
performance and warranty
guidelines please contact your
local Drytac office.

© 2018 Drytac Corporation. E&OE.
All other trademarks are the property
of their respective owners.

Europe

Filwood Road,
Fishponds,
Bristol, BS16 3RY,
United Kingdom
bristol@drytac.com
Tel: +44 (0) 117 958 6500

Canada

105 Nuggett Court,
Brampton,
Ontario, L6T 5A9,
Canada
toronto@drytac.com
Tel: +1 800.353.2883

USA

5601 Eastport Boulevard,
Richmond,
Virginia, 23231,
USA
customerservice@drytac.com
Tel: +1 800.280.6013